

INON

ARM II System

Z Adapter MV

Features

The Z Adapter MV is attached on compatible product to add INON Arm II compatible ball joint to connect to an arm or base product.

The ball joint is made from plastic to provide flexible strobe positioning without loosening a clamp.

How to attach

① When adjusting strobe position

Attach the Z Adapter MV without Fixing Pins if you intend to adjust strobe position during usage.

You can swing the combined strobe on the Z Adapter MV around the M6 thumbscrew to change strobe aiming.

② When fixing strobe position

Attach the Z Adapter MV on a compatible strobe with supplied 2 x Fixing Pins to fix strobe movement on the Z Adapter MV and only ball joint part can be movable.

When using 2 x Fixing Pins, push them in the Z Adapter MV all the way against a plain desk etc. not to make a gap between pin-heads and Z Adapter MV.



Specifications

- Package contents Z Adapter MV x 1 (M6 thumbscrew x 1, washer (white) x 1 and O-ring x 1 are preinstalled) Fixing Pin x 2, Spare O-ring x 1, Spare Washer (white) x 1
- Material Polycarbonate, Aluminium alloy, stainless, rubber
- Dimensions 47.4mm(W) x 75.9mm(H) x 25.9mm(D), 1.9" (W) x 3.0" (H) x 1.0" (D), Effective length 57.8mm(2.3")
- Weight 35.4g (air) / approx.16g (u/w) 1.2oz (air) / approx.0.6oz (u/w)
- Compatible strobe etc. D-2000, D-2000S, D-2000W/Wn, D-180, D-180S, Z-240, Z-220, Z-220S, Z-220F, S-2000, Double Light Holder LE, Quad Light Holder LE, Strobe Light Holder LE

